

Contact us for brand new, refurbished or used HAIDA Equipment AGS-TECH Inc.

Phone: +1-505-550-6501 and +1-505-565-5102; Fax: +1-505-814-5778 Email: sales@agstech.net Web: http://www.agstech.net

Equipment Details For Color Assessment Cabinet

Product image:







Contact us for brand new, refurbished or used HAIDA Equipment AGS-TECH Inc.

Phone: +1-505-550-6501 and +1-505-565-5102; Fax: +1-505-814-5778 Email: sales@agstech.net Web: http://www.agstech.net





Contact us for brand new, refurbished or used HAIDA Equipment AGS-TECH Inc.

Phone: +1-505-550-6501 and +1-505-565-5102; Fax: +1-505-814-5778 Email: sales@agstech.net Web: http://www.agstech.net

Product introduction:

<u>Color Assessment Cabinet</u>, suitable for all industries and applications where there is a need to maintain color consistency and quality-e.g. Automotive, Ceramics, Cosmetics, Foodstuffs, Footwear, Furniture, knitwear, Leather, Ophthalmic, Dyeing, Packaging, Printing, Inks and Textile.

Since different light source has different radiant energy, when they arrive on the surface of an article, different colors display. With regard to color management in industrial production, when a checker has compared the color consistence between products and examples, but there may exist difference between light source used here and light source applied by the client. In such condition, color under different light source differs. It always brings following issues: Client makes complaint for color difference even requires for rejection of goods, seriously damaging company credit.

To resolve the above problem, the most effective way is to check good color under same light source .For example ,international Practice applies Artificial Daylight D65 as standard light source for checking goods color.

It's very important to use standard light source to check color difference in night duty. Besides D65 light source ,TL84,UV, and F/A light sources are available in this Lamp Cabinet for metamerism effect.

Features:

Provide several light sources, i.e. D65, TL84, UV, F/A

Apply microcomputer to switch between the light sources quickly.

Super timing function to record use time of each light source separately.

All fittings are imported, ensuring quality.

Product size is 675mm*455mm*415mm.

Instructions for Light Source:

Name	kelvin	watt	Lamp Type	Uses
D65	6500K	2×18W	Fluorescent Artificial Daylight	International Standard Artificial Daylight
TL84	4000K	2×18W	Fluorescent PHILIPS TLD 18W/840	European,Japan Shop light Source
F/A	2700K	4×40W	Incandescent PHILIPS E27	Sun-settting Light Yellow Light Source
UV	/	1×18W	Fluorescent PHILIPS 18W/BLB	Ultraviolet Lamp

Contact us for brand new, refurbished or used HAIDA Equipment AGS-TECH Inc.

Phone: +1-505-550-6501 and +1-505-565-5102; Fax: +1-505-814-5778 Email: sales@agstech.net Web: http://www.agstech.net

